Rittal – The System.

Faster – better – everywhere.



SK 3237.054

Chopped fiber filter mat

State: 11/17/2026 (Source: www.rittal.com/us-en)

ENCLOSURES POWER DISTRIBUTION CLIMATE CONTROL IT INFRASTRUCTURE SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SK 3237.054 - Chopped fiber filter mat

Replacement filter mats for roof fans, filter fans or thermoelectric coolers to effectively protect control enclosure components from dirt, dust and water.

Features

Model No.	SK 3237.054
Version	for filter fans
Product description	Made of chopped-fiber mat with a progressive construction. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm.
Material	Chemical fibers
Color	White
Note	Not suitable for use in EMC filter fans.
Suitable for Model No.	3237.3xx/3237.7xx
Dimensions	Width: 89 mm Height: 89 mm Depth: 10 mm Width: 3.5 ″ Height: 3.5 ″ Depth: 0.39 ″
Filter class	to DIN EN 779: G2 to DIN EN ISO 16890: ISO coarse 50%
Packaging unit	5 pc(s).
Net weight	0.005 kg
Gross weight	0.012 kg
Customs tariff number	56039390
ETIM 9	EC002513
ETIM 8	EC002513

© Rittal 2026

Features

ECLASS 8.0	27180706
Product description	SK chopped-fiber filter mat, for filter fan SK 3237.7xx/3237.3xx, WHD: 89 x 89 x 10 mm

Approvals

Approvals	CSA UR + C-UR (recognized)