Rittal – The System.

Faster – better – everywhere.



SK 3237.200
Outlet Filters

State: 10/30/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SK 3237.200 - Outlet Filters Standard

For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.



Features

Model No.	SK 3237.200
Product description	For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.
Material	ABS
Color	RAL 7035
Supply includes	Outlet Filters Chopped fiber filter mat
Mounting cut-out	Width of opening: 92 mm Cut-out height: 92 mm Width of opening: 3.62 ″ Cut-out height: 3.62 ″
Suitable for Model No.	SK 3237.1xx
Dimensions	Width: 116.5 mm Height: 116.5 mm Depth: 16 mm Width: 4.59 ″ Height: 4.59 ″ Depth: 0.63 ″
Protection category NEMA	Type 12 with fleece filter Type 3 Type 3R with fleece filter and hose-proof hood

Features

Protection category IP to IEC 60 529	IP 54 with fleece filter IP 56 with fleece filter and hose-proof hood
Packaging unit	1 pc(s).
Net weight	0.1 kg
Gross weight	0.134 kg
Customs tariff number	39269097
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Product description	SK outlet filter, Standard, WHD: 116.5 x 116.5 x 16 mm

Approvals

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)

© Rittal 2026