

# Rittal – The System.

Faster – better – everywhere.



## SK 3237.208 Outlet Filters

State: 6/3/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3237.208 - Outlet Filters Standard

For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.



## Features

Model No.	SK 3237.208
Product description	For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.
Material	ABS
Color	RAL 9005
Supply includes	Outlet Filters Chopped fiber filter mat
Mounting cut-out	Width of opening: 92 mm Cut-out height: 92 mm Width of opening: 3.62 " Cut-out height: 3.62 "
Suitable for Model No.	SK 3237.1xx
Dimensions	Width: 116.5 mm Height: 116.5 mm Depth: 16 mm Width: 4.59 " Height: 4.59 " Depth: 0.63 "
Protection category NEMA	Type 12 with fleece filter Type 3 Type 3R with fleece filter and hose-proof hood

# Features

---

Protection category IP to IEC 60529	IP 54 with fleece filter IP 56 with fleece filter and hose-proof hood
Packaging unit	1 pc(s).
Net weight	0.13 kg
Gross weight	0.14 kg
Customs tariff number	39269097
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Product description	SK outlet filter, standard, WHD: 116.5 x 116.5 x 16 mm

---

# Approvals

---

Approvals	UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK

---