

# Rittal – The System.

Faster – better – everywhere.



## SK 3238.025 Pleated filter

State: 7/10/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3238.025 - Pleated filter for filter and roof-mounted fans, cooling units and chillers

Compared to conventional chopped fiber filters, the high-quality pleated filter technology enables a significant increase in the volume flow and thus an increase in the performance of the unit as well as a reduction in energy consumption. In addition, better filtration properties ensure less dust in the enclosure or unit, and the longer service life means significantly lower service costs.

## Features

Model No.	SK 3238.025
Version	for fan-and-filter units / outlet filters
Material	Pleated filter: base polyester, meltblown polycarbonate Absorber mat: 100% polyester
Color	White
Note	Not suitable for use in EMC filter fans.
Suitable for Model No.	3238.3xx 3238.7xx
Dimensions	Width: 114 mm Height: 114 mm Depth: 14 mm Width: 4.49 " Height: 4.49 " Depth: 0.55 "
Absorber mat dimensions	Width: 120 mm Height: 120 mm
Protection category IP to IEC 60529	IP 55 when mounted in filter fan/outlet filter
Packaging unit	5 pc(s).
Net weight	0.1 kg
Gross weight	0.113 kg
Customs tariff number	56039390

# Features

---

ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Product description	SK folded filter IP55, for filter fan/outlet filter 3238.7xx/3238.3xx, WHD: 114x114x14 mm

# Approvals

---

Approvals	CSA UR + C-UR (recognized)
-----------	-------------------------------