

Rittal – The System.

Faster – better – everywhere.



SK 3238.085 Hose-proof hood

State: 4/25/2026 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3238.085 - Hose-proof hood Carbon steel

The Rittal water-resistant fan shroud fits many indoor and outdoor applications. This painted shroud meets UL Type 3R and Type 4 ratings (model 3237 Type 12, 3R only) for protection from large debris, as well as wind-driven rain and hose-directed water. The blue silicone gasket follows Rittal's innovative legacy in the Food & Beverage industry, leading to better sanitation and cleaning.



Features

Model No.	SK 3238.085
Product description	For fan-and-filter units/outlet filters. When mounted over the fan-and-filter unit and outlet filter, a protection category of IP 56 (UL 3R) to EN 60529/10.91 is achieved. Particularly suitable for use in the food industry.
Material	Carbon steel, powder-coated
Dimensions	Width: 176 mm Height: 245 mm Depth: 55 mm Width: 6.93 " Height: 9.65 " Depth: 2.17 "
Packaging unit	1 pc(s).
Net weight	8.501 lb
Gross weight	8.501 lb
Customs tariff number	8414901080

Approvals

Approvals

Approvals

UL + C-UL - FTTA

UR + C-UR (recognized)