


# Rittal – The System.

Faster – better – everywhere.



## SK 3238.208 Outlet Filters

State: 2/13/2026 (Source: [rittal.com/us-en](https://rittal.com/us-en))



# SK 3238.208 - Outlet Filters Standard

For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.



## Features

Model No.	SK 3238.208
Product description	For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.
Material	ABS
Color	RAL 9005
Supply includes	Outlet Filters Chopped fiber filter mat
Mounting cut-out	Width of opening: 124 mm Cut-out height: 124 mm Width of opening: 4.88 " Cut-out height: 4.88 "
Suitable for Model No.	SK 3238.1xx
Dimensions	Width: 148.5 mm Height: 148.5 mm Depth: 24 mm Width: 5.85 " Height: 5.85 " Depth: 0.94 "

# Features

---

Protection category NEMA	Type 1 with pleated filter Type 12 with fleece filter Type 3 Type 3R Type 4 Type 4X with chopped fiber filter/pleated filter and hose-proof hood
Protection category IP to IEC 60 529	IP 54 with chopped fiber filter/pleated filter IP 55 with pleated filter and absorber mat IP 56 with chopped fiber filter/pleated filter and hose-proof hood
Packaging unit	1 pc(s).
Net weight	0.17
Gross weight	0.18
Customs tariff number	39269097
EAN	4028177663466
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

---

# Approvals

---

Approvals	UL + C-UL - FTTA UR + C-UR (recognized)
Certificates	EAC
Explanations	Declaration of conformity Declaration of conformity UK

---