



**Rittal – The System.**

Faster – better – everywhere.



**SK 3239.066**

**Chopped fiber filter mat**

State: 7/27/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3239.066 - Chopped fiber filter mat

Replacement filter mats for roof fans, filter fans or thermoelectric coolers to effectively protect control enclosure components from dirt, dust and water.

## Features

Model No.	SK 3239.066
Version	for EMC filter fans
Product description	Made of chopped-fiber mat with a progressive construction. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm.
Material	Copper/nickel/chrome-coated chemical fibers
Note	Performance data, protection category, and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.
Suitable for Model No.	3239.6..
Dimensions	Width: 178 mm Height: 178 mm Depth: 17 mm Width: 7.01 " Height: 7.01 " Depth: 0.67 "
Filter class	to DIN EN 779: G3
Packaging unit	5 pc(s).
Net weight	0.05
Gross weight	0.054
Customs tariff number	56039390
EAN	4028177666238
ETIM 9	EC002513
ETIM 8	EC002513

# Features

---

ECLASS 8.0	27180706
------------	----------

# Approvals

---

Approvals	UR + C-UR (recognized)
Certificates	EAC