

Rittal – The System.

Faster – better – everywhere.



SK 3239.308 Blue e+ outlet filter

State: 8/20/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3239.308 - Blue e+ outlet filter

The outlet filter is used in conjunction with the associated filter fan to dissipate lost heat out of the enclosures, to ventilate the enclosure and to protect temperature-sensitive components. This is done via the direct supply of ambient air that must be below the permissible temperature inside the enclosure.



Features

| | |
|------------------------|---|
| Model No. | SK 3239.308 |
| Version | wall-mounted |
| Benefits | Easy filter change thanks to a new opening mechanism on the louvre grille Faster assembly on the enclosure due to optimized snap hooks Tool-free mounting |
| Material | Plastic |
| Color | RAL 9005 |
| Supply includes | Outlet Filters Pleated filter |
| Mounting cut-out | Width of opening: 177 mm Cut-out height: 177 mm Width of opening: 6.97 " Cut-out height: 6.97 " |
| Suitable for Model No. | SK 3239.7xx |

Features

| | |
|-------------------------------------|--|
| Dimensions | Width: 204 mm Height: 204 mm Depth: 45.8 mm Width: 8.03 " Height: 8.03 " Depth: 1.8 " |
| Protection category NEMA | Type 12 with chopped fiber filter/pleated filter Type 3, 3R, 4, 4X with chopped fiber filter/pleated filter and hose-proof hood |
| Protection category IP to IEC 60529 | IP 54 with chopped fiber filter/pleated filter IP 55 with pleated filter and absorber mat IP 56 with chopped fiber filter/pleated filter and hose-proof hood |
| Packaging unit | 1 pc(s). |
| Net weight | 0.37 |
| Gross weight | 0.47 |
| Customs tariff number | 39269097 |
| EAN | 4028177998384 |
| ETIM 9 | EC002513 |
| ETIM 8 | EC002513 |
| ECLASS 8.0 | 27180706 |

Approvals

| | |
|-----------|--|
| Approvals | UL + C-UL - FTTA UR + C-UR (recognized) |
|-----------|--|