Rittal – The System.

Faster – better – everywhere.





SK 3240.080 Hose-proof hood

State: 11/27/2025 (Source: rittal.com/us-en)



SK 3240.080 - Hose-proof hood Stainless steel

The Rittal stainless steel fan shroud is engineered for rugged indoor and outdoor use. Its durable finish carries UL Type 3R and 4X certifications (model 3237 Type 12, 3R only) to guard against large debris, heavy rain, hose-directed water sprays, and corrosion. A blue silicone gasket—rooted in Rittal's Food & Beverage expertise—ensures superior hygiene and simplifies washdown cleaning.







Features

Model No.	SK 3240.080
Product description	For fan-and-filter units/outlet filters. Easy cleaning thanks to external, food-safe silicone seal.
Material	Stainless steel AISI304 - 1.4301 (V2A) Silicone
Suitable for Model No.	3240 3241
Dimensions	Width: 282 mm Height: 390 mm Depth: 85 mm Width: 11.1 " Height: 15.4 " Depth: 3.35 "
Protection category NEMA	NEMA 1 NEMA 12 NEMA 3 NEMA 3R NEMA 4 NEMA 4X

© Rittal 2025

Features

Protection category IP to IEC 60 529	IP 56 when fitted over fan-and-filter unit/outlet filter with filter mat
Packaging unit	1 pc(s).
Net weight	3.123
Gross weight	3.323
Customs tariff number	94039910
EAN	4028177651920
ETIM 9	EC000744
ETIM 8	EC000744
ECLASS 8.0	27182405

Approvals

Approvals	CSA
	UL + C-UL - FTTA
	UR + C-UR (recognized)
Certificates	EAC

© Rittal 2025 3