Rittal – The System.

Faster - better - everywhere.





SK 3240.200 **Outlet Filters**

State: 11/26/2025 (Source: rittal.com/us-en)



SK 3240.200 - Outlet Filters Standard

For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.



Features

Model No.	SK 3240.200
Product description	For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.
Material	ABS
Color	RAL 7035
Supply includes	Outlet Filters
	Chopped fiber filter mat
Mounting cut-out	Width of opening: 224 mm
	Cut-out height: 224 mm
	Width of opening: 8.82 "
	Cut-out height: 8.82 "
Suitable for Model No.	3240.1xx/3240.5xx/3241.1xx/3241.5xx
Dimensions	Width: 255 mm
	Height: 255 mm
	Depth: 25 mm
	Width: 10 "
	Height: 10 "
	Depth: 0.98 "

© Rittal 2025

Features

Protection category NEMA	Type 12 with chopped fiber filter/pleated filter Type 3 Type 3R
	Type 4
	Type 4X with chopped fiber filter/pleated filter and hose-proof hood
Protection category IP to IEC 60	IP 54 with chopped fiber filter/pleated filter
529	IP 55 with pleated filter and absorber mat
	IP 56 with chopped fiber filter/pleated filter and hose-proof hood
Packaging unit	1 pc(s).
Net weight	0.56
Gross weight	0.582
Customs tariff number	39269097
EAN	4028177651975
E-Number Sweden	E3404361
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

Approvals

Approvals	CSA
	UL + C-UL - FTTA
	UR + C-UR (recognized)
Certificates	EAC
Explanations	Declaration of conformity

© Rittal 2025 3