Rittal – The System.

Faster – better – everywhere.


SK 3243.080

Hose-proof hood

State: 11/21/2026 (Source: www.rittal.com/us-en)

SK 3243.080 - Hose-proof hood Stainless steel

The Rittal stainless steel fan shroud is engineered for rugged indoor and outdoor use. Its durable finish carries UL Type 3R and 4X certifications (model 3237 Type 12, 3R only) to guard against large debris, heavy rain, hose-directed water sprays, and corrosion. A blue silicone gasket—rooted in Rittal's Food & Beverage expertise—ensures superior hygiene and simplifies washdown cleaning.



Features

Model No.	SK 3243.080
Product description	For fan-and-filter units/outlet filters. Easy cleaning thanks to external, food-safe silicone seal.
Material	Stainless steel AISI304 - 1.4301 (V2A) Silicone
Suitable for Model No.	3243.... 3244....
Dimensions	Width: 350 mm Height: 480 mm Depth: 110 mm Width: 13.8 ″ Height: 18.9 ″ Depth: 4.33 ″
Protection category NEMA	NEMA 1 NEMA 12 NEMA 3 NEMA 3R NEMA 4 NEMA 4X

© Rittal 2026

Features

Protection category IP to IEC 60 529	IP 56 when fitted over fan-and-filter unit/outlet filter with filter mat
Packaging unit	1 pc(s).
Net weight	3.8 kg
Gross weight	4.102 kg
Customs tariff number	73269098
ETIM 9	EC000744
ETIM 8	EC000744
ECLASS 8.0	27182405
Product description	SK hose-proof hood, for SK 3243…/3244…, WHD: 350 x 480 x 110 mm

Approvals

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)