

Rittal – The System.

Faster – better – everywhere.



SK 3243.200 Outlet Filters

State: 5/22/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3243.200 - Outlet Filters Standard

For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.



Features

Model No.	SK 3243.200
Product description	For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.
Material	ABS
Color	RAL 7035
Supply includes	Outlet Filters Chopped fiber filter mat
Mounting cut-out	Width of opening: 292 mm Cut-out height: 292 mm Width of opening: 11.5 " Cut-out height: 11.5 "
Suitable for Model No.	SK 3243.1xx/3243.5xx/3244.1xx/3244.5xx/3245.5xx
Dimensions	Width: 323 mm Height: 323 mm Depth: 25 mm Width: 12.7 " Height: 12.7 " Depth: 0.98 "

Features

Protection category NEMA	Type 12 with chopped fiber filter/pleated filter Type 3 Type 3R Type 4 Type 4X with chopped fiber filter/pleated filter and hose-proof hood
Protection category IP to IEC 60529	IP 54 with chopped fiber filter/pleated filter IP 55 with pleated filter and absorber mat IP 56 with chopped fiber filter/pleated filter and hose-proof hood
Packaging unit	1 pc(s).
Net weight	0.737 kg
Gross weight	0.82 kg
Customs tariff number	39269097
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Product description	SK outlet filter, Standard, WHD: 323 x 323 x 25 mm

Approvals

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity
