Rittal - The System.

Faster - better - everywhere.





SK 3243.208 Outlet Filters

State: 11/17/2025 (Source: rittal.com/us-en)



SK 3243.208 - Outlet Filters Standard

For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.



Features

Model No.	SK 3243.208
Product description	For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.
Material	ABS
Color	RAL 9005
Supply includes	Outlet Filters
	Chopped fiber filter mat
Mounting cut-out	Width of opening: 292 mm
	Cut-out height: 292 mm
	Width of opening: 11.5 "
	Cut-out height: 11.5 "
Suitable for Model No.	SK 3243.1xx/3243.5xx/3244.1xx/3244.5xx/3245.5xx
Dimensions	Width: 323 mm
	Height: 323 mm
	Depth: 25 mm
	Width: 12.7 "
	Height: 12.7 "
	Depth: 0.98 "

© Rittal 2025

Features

Protection category NEMA	Type 12 with chopped fiber filter/pleated filter Type 3
	Type 3R
	Type 4
	Protection category IP to IEC 60
529	IP 55 with pleated filter and absorber mat
	IP 56 with chopped fiber filter/pleated filter and hose-proof hood
Packaging unit	1 pc(s).
Net weight	0.75
Gross weight	0.811
Customs tariff number	39269097
EAN	4028177663879
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

Approvals

Approvals	UL + C-UL - FTTA UR + C-UR (recognized)
Certificates	EAC
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2025 3