

Rittal – The System.

Faster – better – everywhere.



SK 3245.080 Hose-proof hood

State: 11/17/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3245.080 - Hose-proof hood Stainless steel

The Rittal stainless steel fan shroud is engineered for rugged indoor and outdoor use. Its durable finish carries UL Type 3R and 4X certifications (model 3237 Type 12, 3R only) to guard against large debris, heavy rain, hose-directed water sprays, and corrosion. A blue silicone gasket—rooted in Rittal’s Food & Beverage expertise—ensures superior hygiene and simplifies washdown cleaning.



Features

Model No.	SK 3245.080
Product description	For fan-and-filter units/outlet filters. Easy cleaning thanks to external, food-safe silicone seal.
Material	Stainless steel AISI304 - 1.4301 (V2A) Silicone
Suitable for Model No.	3245....
Dimensions	Width: 350 mm Height: 480 mm Depth: 160 mm Width: 13.8 “ Height: 18.9 “ Depth: 6.3 “
Protection category NEMA	NEMA 1 NEMA 12 NEMA 3 NEMA 3R
Protection category IP to IEC 60529	IP 56 when fitted over fan-and-filter unit/outlet filter with filter mat

Features

Packaging unit	1 pc(s).
Net weight	5.32
Gross weight	5.6
Customs tariff number	94039910
EAN	4028177655522
ETIM 9	EC000744
ETIM 8	EC000744
ECLASS 8.0	27182405

Approvals

Certificates	EAC
--------------	-----