


Rittal – The System.

Faster – better – everywhere.



SK 3300.040

TS 8 section door for climate module concept

State: 12/22/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3300.040 - TS 8 section door for climate module concept for installing cooling modules

Carbon steel section doors to accommodate SK 3307.7XX to 3310.7XX climate control modules.



Features

Model No.	SK 3300.040
Product description	Carbon steel section doors to accommodate SK 3307.7XX to 3310.7XX climate control modules.
Material	Carbon steel
Color	RAL 7035
Supply includes	Section door without preassembled cooling module TS 8 hinges, door opening angle approx. 110°
Note	The following information applies to 1200 mm wide TS 8 enclosures With the unit positioned on the right, one pack consists of a section door for installing in the right-hand half of the enclosure plus a special lockable door for the left-hand half. With the unit positioned on the left, one pack consists of a section door for installing in the left-hand half of the enclosure. The existing lockable door on the right may be used.
Note on Model No.:	R/h door catch
Suitable for	Enclosure type: TS 8: = 600 mm: = 1,800 mm Enclosure type: TS 8: = 23.6 " : = 70.9 "
Packaging unit	1 pc(s).
Net weight	21

Features

Gross weight	24
EAN	4028177560024
ECLASS 8.0	27180702

Approvals

Certificates	EAC
--------------	-----