

Rittal – The System.

Faster – better – everywhere.



SK 3301.380

Vertical shielding

State: 4/25/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3301.380 - Vertical shielding for TS IT

To block the airflow to the left and right of the 19" level, for enclosure height 2000 mm.

Features

Model No.	SK 3301.380
Version	Self-adhesive on one side
Product description	To block the airflow on the left and right of the 19" level, for enclosure height 2000 mm.
Material	Cellular PU foam Flame-inhibiting to UL 94 (HF1)
Color	Anthracite
For sealing between	Side panel and 482.6 mm (19") level
Dimensions	Width: 84 mm Height: 1,910 mm Depth: 84 mm Width: 3.31 " Height: 75.2 " Depth: 3.31 "
Suitable for	Width: 600 mm Width: 23.6 "
Packaging unit	1 pc(s).
Net weight	0.402 kg
Gross weight	0.502 kg
Customs tariff number	39269097
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Product description	SK Vertical shielding, Sealing between side panel/LCP and 482.6 mm (19") level, WHD: 84x1910x84 mm, Cellular PU foam, self-adhesive on one side