## Rittal - The System.

Faster - better - everywhere.





## SK 3313.614 Connection hose

State: 11/18/2025 (Source: rittal.com/us-en)



## SK 3313.614 - Connection hose

Flexible connection hose, may be shortened, including union nuts on both sides for connecting the LCP/LCU to existing pipework.

## **Features**

Model No.	SK 3313.614
Version	Rack cooling CW
Product description	The water connection kit provides a simple cooling water connection from the LCU to fixed on-site pipework. The hoses have a 90° bend on one side and a clamping shell on the other side, which allows the hoses to be shortened.
Material	NBR (inner) with steel spiral and fabric insert
Length	2.5 m 98.4 ″
Water connections	G ¾" internal thread
Operating temperature range	-30 °C70 °C -22 °F158 °F
Permissible operating pressure (p. max.)	10 bar 145 PSI
Packaging unit	2 pc(s).
Net weight	5.08
Gross weight	5.485
Customs tariff number	39173200
EAN	4028177983861
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712

© Rittal 2025