

**Rittal – The System.**

Faster – better – everywhere.



# SK 3313.614 Connection hose

State: 6/23/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3313.614 - Connection hose

Flexible connection hose, may be shortened, including union nuts on both sides for connecting the LCP/LCU to existing pipework.

## Features

Model No.	SK 3313.614
Version	Rack cooling CW
Product description	The water connection kit provides a simple cooling water connection from the LCU to fixed on-site pipework. The hoses have a 90° bend on one side and a clamping shell on the other side, which allows the hoses to be shortened.
Material	NBR (inner) with steel spiral and fabric insert
Length	2.5 m 98.4 "
Water connections	G ¾" internal thread
Operating temperature range	-30 °C...70 °C -22 °F...158 °F
Permissible operating pressure (p. max.)	10 bar 145 PSI
Packaging unit	2 pc(s).
Net weight	5.08 kg
Gross weight	5.485 kg
Customs tariff number	39173200
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712
Product description	SK connection hose, for LCU CW 3313.610, length 2500 mm