## Rittal – The System.

Faster – better – everywhere.





# SK 3321.705 Chopped fiber filter mat

State: 11/2/2025 (Source: rittal.com/us-en)



## SK 3321.705 - Chopped fiber filter mat

Replacement filter mats for roof fans, filter fans or thermoelectric coolers to effectively protect control enclosure components from dirt, dust and water.

#### **Features**

Model No.	SK 3321.705		
Version	for filter fans		
Product description	Made of chopped-fiber mat with a progressive construction. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 μm.		
Material	Chemical fibers		
Note	Performance data, protection category, and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.		
Suitable for Model No.	3237.2xx/3237.1xx		
Dimensions	Width: 89 mm Height: 89 mm Depth: 10 mm Width: 3.5 " Height: 3.5 " Depth: 0.39 "		
Filter class	to DIN EN 779: G2 to DIN EN ISO 16890: ISO coarse 50%		
Packaging unit	50 pc(s).		
Net weight	0.1		
Gross weight	0.156		
Customs tariff number	56039390		
EAN	4028177695535		
ETIM 9	EC002513		

© Rittal 2025

### Features

ETIM 8	EC002513
ECLASS 8.0	27180706

## **Approvals**

Certificates EAC	Certificates	EAC		
------------------	--------------	-----	--	--

© Rittal 2025 3