## Rittal – The System.

Faster – better – everywhere.





## SK 3322.720 Pleated filter

State: 12/9/2025 (Source: rittal.com/us-en)



# SK 3322.720 - Pleated filter for filter and roof-mounted fans, cooling units and chillers

Compared to conventional chopped fiber filters, the high-quality pleated filter technology enables a significant increase in the volume flow and thus an increase in the performance of the unit as well as a reduction in energy consumption. In addition, better filtration properties ensure less dust in the enclosure or unit, and the longer service life means significantly lower service costs.



#### **Features**

Model No.	SK 3322.720
Version	for fan-and-filter units / outlet filters
Material	PET
Color	White
Note	Performance data, protection category, and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.
Suitable for Model No.	3238.xxx
Dimensions	Width: 114 mm
	Height: 114 mm
	Depth: 14 mm
	Width: 4.49 "
	Height: 4.49 "
	Depth: 0.55 "
Filter class	to DIN EN 779: G4
	to DIN EN ISO 16890: ISO coarse 70%
Protection category IP to IEC 60 529	IP 54 when mounted in filter & roof-mounted fans/outlet filters

© Rittal 2025 2

### Features

Not suitable for use in EMC filter fans. 5 pc(s).
5 pc(s).
0.095
0.1
56039390
4028177969162
EC002513
EC002513
27180706

## Approvals

Approvals	UR + C-UR (recognized)

© Rittal 2025 3