Rittal - The System.

Faster - better - everywhere.





SK 3342.024

Rack-mounted fans for 482.6 mm (19")

State: 10/29/2025 (Source: rittal.com/us-en)



SK 3342.024 - Rack-mounted fans for 482.6 mm (19") Air throughput 188.34 - 282..52 cfm

Rack-mounted fan for direct installation in the 19" level. Installation allows air to circulate permanently inside the enclosure, which prevents the creation of hot spots.

Features

| Model No. | SK 3342.024 |
|-------------------------------------|---|
| Product description | Rack-mounted fan for direct installation in the 19" level. The installation enables permanent air circulation in the enclosure, which prevents the creation of hot spots. |
| Color | RAL 7035 |
| Supply includes | Wired unit ready for connection Incl. terminal strip and assembly components |
| Air throughput (unimpeded air flow) | 480 m³/h 282.5 cfm |
| Note on Model No.: | Delivery times on request. |
| Rated operating voltage | 24 V (DC) |
| Rated current max. | with DC: 0.74 A |
| Pre-fuse | Miniature circuit-breaker/fuse: 6 A |
| Dimensions | Width: 482.6 mm Height: 44 mm Depth: 200 mm Width: 19 " Height: 1.73 " Depth: 7.87 " |
| Distance between fan axes | 105 mm 4.13 ″ |
| Number of fans | 3 |
| Noise pressure level | with DC: 51 dB(A) |

© Rittal 2025 2

Features

| Operating temperature range | -10 °C55 °C |
|-----------------------------|---------------|
| | 14 °F131 °F |
| Packaging unit | 1 pc(s). |
| Net weight | 1.75 |
| Gross weight | 1.86 |
| Customs tariff number | 84145915 |
| EAN | 4028177041509 |
| ETIM 9 | EC000320 |
| ETIM 8 | EC000320 |
| ECLASS 8.0 | 27180716 |
| | |

Approvals

| Approvals | UR + C-UR (recognized) VDE |
|--------------|-------------------------------|
| Explanations | Declaration of conformity |

© Rittal 2025 3