Rittal – The System.

Faster – better – everywhere.



SK 3375.510

Air-Water Heat Exchangers

State: 11/10/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SK 3375.510 - Air-Water Heat Exchangers wall-mounted

Output categories 1023.64 - 17060.71 BTU/h. For use in tough environments. Convenient mounting options and flexible water connection options. External mounting or full internal mounting possible.

Features

Model No.	SK 3375.510
Version	wall-mounted Water-carrying parts copper/brass (Cu/CuZn)
Product description	To be used in rough environments and temperature ranges of up to +70 °C. Convenient assembly options and flexible water connection options. Partial or full internal mounting possible.
Color	RAL 7035
Supply includes	Wired ready for connection Drilling template Sealing and assembly components
Total cooling output	L 35 W 10 at 400 l/h: 5 kW L 35 W 10 at 400 l/h: 17,061 BTU/h
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz 110 V (DC)
Rated power Pel	At 50 Hz: 178 W At 60 Hz: 232 W
Rated current max.	At 50 Hz: 2.25 A At 60 Hz: 2.25 A
Permissible operating pressure (p. max.)	1: 10 bar 14.5: 145 PSI
Duty cycle	100 %
Cooling medium	Water (see Internet for specifications)
Water inlet temperature	1 °C...30 °C 34 °F...86 °F

© Rittal 2026

Features

Water connections	½" connector sleeve G ⅜" external thread
Temperature control	e-Comfort Controller (factory setting +35 °C)
Operating temperature range	1 °C...70 °C 34 °F...158 °F
Note	Integral non-return valve for version with e-Comfort controller
Dimensions	Width: 450 mm Height: 1,400 mm Depth: 220 mm Width: 17.7 ″ Height: 55.1 ″ Depth: 8.66 ″
Note on Model No.:	Delivery times on request.
Setting range	20 °C...55 °C 68 °F...131 °F
Pre-fuse	Transformer circuit-breaker: 3.5...5 A
Protection category IP to EN 60 529	IP 55
Protection category NEMA	UL Type 1 UL Type 3R UL Type 12
Packaging unit	1 pc(s).
Net weight	96.561 lb
Gross weight	101.411 lb
CRA risk class	Default (Low Risk)
Customs tariff number	8415830070
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712

Features

Product description	SK Air/water heat exchanger, wall-mounted, 17061 BTU/h, 115 V, 1~, 50/60 Hz, comfort controller, water-carrying parts: copper/ brass, WHD: 450 x 1400 x 220 mm

Approvals

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity