
Rittal – The System.

Faster – better – everywhere.





SV 3450.500 Conductor terminal

State: 12/1/2025 (Source: rittal.com/us-en)



SV 3450.500 - Conductor terminal

For connecting round conductors and laminated copper bars.

Features

Model No.	SV 3450.500
Product description	For connecting round conductors and laminated copper bars.
Material	Carbon steel
Surface finish	Zinc-plated, passivated
Note	Wire end ferrules should be used with fine stranded wire conductors
Connection of round conductors	1 - 4 mm²
For busbar thickness	5 mm 0.2 ″
Packaging unit	15 pc(s).
Net weight	0.225
Gross weight	0.278
PCF/VE (cradle-to-gate)	1 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	85369010
EAN	4028177042674
ETIM 9	EC000001
ETIM 8	EC000001
ECLASS 8.0	27141146

Approvals

© Rittal 2025

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3