

Rittal – The System.

Faster – better – everywhere.



SV 3460.500 Plate Clamp

State: 4/26/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3460.500 - Plate Clamp

For connecting laminated copper bars, no drilling required.

Features

| | |
|---|--|
| Model No. | SV 3460.500 |
| Product description | For connecting laminated copper bars, no drilling required. |
| Material | Carbon steel |
| Surface finish | Zinc-plated, passivated |
| Clamping area for laminated copper bars (W x H) | 65 x 10 mm 2.56 x 0.39 " |
| Suitable for busbars | 80 x 10 |
| Suitable for busbars | Busbar E-Cu |
| Packaging unit | 3 pc(s). |
| Net weight | 2.1 kg |
| Gross weight | 2.202 kg |
| PCF/VE (cradle-to-gate) | 8.4 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 85369010 |
| ETIM 9 | EC000001 |
| ETIM 8 | EC000001 |
| ECLASS 8.0 | 27141146 |
| Product description | SV Plate clamp, for laminated copper bar, clamping area WH: 65x10 mm, for busbar WH: 80x10 mm |

Approvals

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK