
Rittal – The System.

Faster – better – everywhere.



SV 3555.000

Conductor terminal

State: 11/1/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 3555.000 - Conductor terminal

For connecting round conductors and laminated copper bars.

Features

Model No.	SV 3555.000
Product description	For connecting round conductors and laminated copper bars.
Material	Brass
Note	Wire end ferrules should be used with fine stranded wire conductors
Connection of round conductors	1 - 4 mm²
For busbar thickness	6 - 10 mm 0.24 - 0.39 ″
Packaging unit	15 pc(s).
Net weight	0.345 kg
Gross weight	0.401 kg
PCF/VE (cradle-to-gate)	1.5 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	85369010
ETIM 9	EC000001
ETIM 8	EC000001
ECLASS 8.0	27141146
Product description	SV Conductor connection clamp, 1-4 mm², for bar thickness 6-10 mm, brass

Approvals

Approvals

Explanations

Declaration of conformity
Declaration of conformity UK