

Rittal – The System.

Faster – better – everywhere.



TS 3659.180

Server telescopic slides

State: 12/21/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 3659.180 - Server telescopic slides

For optimal server access - even when installed.

Features

Model No.	TS 3659.180
Version	For distance between levels of 468.6-687.4 mm
Product description	Ensure optimum accessibility to the server, even when built-in. For servers with a max. width of 426 mm.
Material	Carbon steel
Supply includes	Telescopic slide with mounting kit Mounting accessories
Pull-out depth	511.2 mm 20.1 "
Suitable for	Enclosure type: TS: 600 mm Enclosure type: TS IT Enclosure type: VX IT Enclosure type: TS: 23.6 " Enclosure type: TS IT Enclosure type: VX IT
Load capacity	30 kg
Note	Only in conjunction with L-shaped profile rails
Packaging unit	2 pc(s).
Net weight	2.424
Gross weight	2.624
Customs tariff number	73269098
EAN	4028177222908
ETIM 9	EC002520
ETIM 8	EC002520
ECLASS 8.0	27189261