

Rittal – The System.

Faster – better – everywhere.



IT 3659.191

Server telescopic slides

State: 4/26/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 3659.191 - Server telescopic slides for IT enclosure systems and IT enclosures

Ensure optimum accessibility to the server, even when built-in. For servers with a max. width of 430 mm.



Features

| | |
|---------------------|--|
| Model No. | IT 3659.191 |
| Version | For level spacing of 573.65 - 701.65 mm |
| Product description | Ensure optimum accessibility to the server, even when built-in. For servers with a max. width of 430 mm. |
| Material | Carbon steel |
| Load capacity | 30 kg |
| Note | Only in conjunction with L-shaped profile rails |
| Suitable for | Enclosure type: TS TS IT VX VX IT Depth: = 800 mm Enclosure type: TS TS IT VX VX IT Depth: = 31.5 " |
| Packaging unit | 2 pc(s). |
| Net weight | 2.82 kg |
| Gross weight | 3.08 kg |

Features

| | |
|-------------------------------------|--|
| PCF/VE (cradle-to-gate) | 6 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ETIM 8 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | Server telescopic rails for TS, TS IT, VX, VX IT, for depth 800 mm, extension: 573 mm, for server with maximum width of 430 mm |