

Rittal – The System.

Faster – better – everywhere.



HD 4000.081 Viewing window HD

State: 6/14/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 4000.081 - Viewing window HD

To protect keys or displays.

Features

Model No.	HD 4000.081
Product description	To protect keys or displays.
Benefits	Wide field of vision Gap-free transition between viewing window and frame External hinge With T-handle for easy opening without keys
Material	Frame: Stainless steel 1.4301 (AISI 304) Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600 Viewing window: Polycarbonate
Supply includes	Including 2 hinges Including T-handle Assembly components
Visible area	Viewing window width: 212 mm Viewing window height: 90 mm Viewing window width: 8.35 " Viewing window height: 3.54 "
Dimensions	Width: 330 mm Height: 190 mm Depth: 65 mm Width: 13 " Height: 7.48 " Depth: 2.56 "
Suitable for	Enclosure type: Compact enclosure HD
Protection category IP to IEC 60529	IP 55
IK code	IK08
Installation options	For external mounting on surfaces.

Features

Type rating according to UL 50E	Type 1 Type 12 Type 13
Packaging unit	1 pc(s).
Net weight	1.83 kg
Gross weight	1.891 kg
Customs tariff number	39252000
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182204
Product description	HD viewing window, with toggle handle, WxH: 330x190 mm, stainless steel, 1.4301
