Rittal - The System.

Faster – better – everywhere.





HD 4000.083 Viewing window HD

State: 11/19/2025 (Source: rittal.com/us-en)



HD 4000.083 - Viewing window HD

To protect keys or displays.

Features

Model No.	HD 4000.083
Product description	To protect keys or displays.
Benefits	Wide field of vision
	Gap-free transition between viewing window and frame
	External hinge
	With T-handle for easy opening without keys
Material	Frame: Stainless steel 1.4301 (AISI 304)
	Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600
	Viewing window: Polycarbonate
Supply includes	Including 2 hinges
	Including T-handle
	Assembly components
Visible area	Viewing window width: 400 mm
	Viewing window height: 330 mm
	Viewing window width: 15.7 ″
	Viewing window height: 13 "
Dimensions	Width: 518 mm
	Height: 436 mm
	Depth: 65 mm
	Width: 20.4 "
	Height: 17.2 "
	Depth: 2.56 "
Suitable for	Enclosure type: Compact enclosure HD
Protection category IP to IEC 60 529	IP 55
IK code	IK08
Installation options	For external mounting on surfaces.

© Rittal 2025

Features

Type rating according to UL 50E	Type 1
	Type 12
	Type 13
Packaging unit	1 pc(s).
Net weight	4.15
Gross weight	4.206
Customs tariff number	39252000
EAN	4028177985155
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182204

© Rittal 2025 3