Rittal – The System.

Faster – better – everywhere.



HD 4000.083

Viewing window HD

State: 10/31/2026 (Source: www.rittal.com/us-en)

HD 4000.083 - Viewing window HD

To protect keys or displays.

Features

Model No.	HD 4000.083
Product description	To protect keys or displays.
Benefits	Wide field of vision Gap-free transition between viewing window and frame External hinge With T-handle for easy opening without keys
Material	Frame: Stainless steel 1.4301 (AISI 304) Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600 Viewing window: Polycarbonate
Supply includes	Including 2 hinges Including T-handle Assembly components
Visible area	Viewing window width: 400 mm Viewing window height: 330 mm Viewing window width: 15.7 ″ Viewing window height: 13 ″
Dimensions	Width: 518 mm Height: 436 mm Depth: 65 mm Width: 20.4 ″ Height: 17.2 ″ Depth: 2.56 ″
Suitable for	Enclosure type: Compact enclosure HD
Protection category IP to IEC 60 529	IP 55
IK code	IK08
Installation options	For external mounting on surfaces.

Features

Type rating according to UL 50E	Type 1 Type 12 Type 13
Packaging unit	1 pc(s).
Net weight	4.15 kg
Gross weight	4.206 kg
Customs tariff number	39252000
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182204
Product description	HD viewing window, with toggle handle, WxH: 518x436 mm, stainless steel, 1.4301

© Rittal 2026