## Rittal – The System.

Faster - better - everywhere.





# HD 4000.240 HD Leveling Feet

State: 10/29/2025 (Source: rittal.com/us-en)



## HD 4000.240 - HD Leveling Feet

HD leveling feet to minimize cleaning time thanks to fully covered, permanently sealed thread. Also compensates for floor inclines of up to 10° thanks to the flexible base plate.

#### **Features**

Model No.	HD 4000.240	
Version	Without base mounting bracket	
Benefits	Minimizes cleaning time due to fully covered, permanently sealed threads  Compensation of floor inclines up to an angle of 10° thanks to flexible base plate  Leveling of bayed enclosures can be achieved on sloping floors, thanks to a large leveling range  Certification according to 3-A Sanitary standards	
Material	Stainless steel 1.4301 (AISI 304)	
Supply includes	Assembly components and seals	
Load capacity	Max. 7000 N static per leveling foot	
Dimensions	Thread: M12	
Suitable for	Enclosure type: Compact enclosure HD VX VX SE TS	
Leveling range	122 - 175 mm 4.8 - 6.89 ″	
Packaging unit	4 pc(s).	
Net weight	2	
Gross weight	2.342	
Customs tariff number	73181900	
EAN	4028177707641	
ETIM 9	EC002622	

© Rittal 2025 2

### **Features**

ETIM 8	EC002622	
ECLASS 8.0	27189263	

© Rittal 2025 3