

# Rittal – The System.

Faster – better – everywhere.



## HD 4000.240 HD Leveling Feet

State: 6/15/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# HD 4000.240 - HD Leveling Feet

HD leveling feet to minimize cleaning time thanks to fully covered, permanently sealed thread. Also compensates for floor inclines of up to 10° thanks to the flexible base plate.

## Features

|                       |   |
|-----------------------|---|
| Model No.             | HD 4000.240   |
| Version               | Without base mounting bracket   |
| Benefits              | Minimizes cleaning time due to fully covered, permanently sealed threads<br>Compensation of floor inclines up to an angle of 10° thanks to flexible base plate<br>Leveling of bayed enclosures can be achieved on sloping floors, thanks to a large leveling range<br>Certification according to 3-A Sanitary standards |
| Material              | Stainless steel 1.4301 (AISI 304)   |
| Supply includes       | Assembly components and seals   |
| Load capacity         | Max. 7000 N static per leveling foot  |
| Dimensions            | Thread: M12   |
| Suitable for          | Enclosure type: Compact enclosure HD<br>VX<br>VX SE<br>TS   |
| Leveling range        | 122 - 175 mm<br>4.8 - 6.89 "  |
| Packaging unit        | 4 pc(s).  |
| Net weight            | 2 kg  |
| Gross weight          | 2.342 kg  |
| Customs tariff number | 73181900  |
| ETIM 9                | EC002622  |
| ETIM 8                | EC002622  |

# Features

---

ECLASS 8.0

27189263

---

Product description

HD Levelling foot, without base mount, Stainless steel 1.4301