

Rittal – The System.

Faster – better – everywhere.



HD 4000.250 HD Leveling Feet

State: 7/7/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 4000.250 - HD Leveling Feet

HD leveling feet to minimize cleaning time thanks to fully covered, permanently sealed thread. Also compensates for floor inclines of up to 10° thanks to the flexible base plate.

Features

Model No.	HD 4000.250
Version	With base mounting bracket
Benefits	Minimizes cleaning time due to fully covered, permanently sealed threads Compensation of floor inclines up to an angle of 10° thanks to flexible base plate Leveling of bayed enclosures can be achieved on sloping floors, thanks to a large leveling range Certification according to 3-A Sanitary standards
Material	Stainless steel 1.4301 (AISI 304)
Supply includes	Assembly components and seals
Load capacity	Max. 7000 N static per leveling foot
Dimensions	Thread: M12
Suitable for	Enclosure type: Compact enclosure HD VX VX SE TS
Leveling range	122 - 175 mm 4.8 - 6.89 "
Packaging unit	4 pc(s).
Net weight	2.4 kg
Gross weight	2.5 kg
Customs tariff number	73181900
ETIM 9	EC002622
ETIM 8	EC002622

Features

ECLASS 8.0

27189263

Product description

HD Levelling foot, with base mount, Stainless steel 1.4301