

Rittal – The System.

Faster – better – everywhere.



HD 4000.250 HD Leveling Feet

State: 12/10/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 4000.250 - HD Leveling Feet

HD leveling feet to minimize cleaning time thanks to fully covered, permanently sealed thread. Also compensates for floor inclines of up to 10° thanks to the flexible base plate.

Features

| | |
|-----------------------|---|
| Model No. | HD 4000.250 |
| Version | With base mounting bracket |
| Benefits | Minimizes cleaning time due to fully covered, permanently sealed threads Compensation of floor inclines up to an angle of 10° thanks to flexible base plate Leveling of bayed enclosures can be achieved on sloping floors, thanks to a large leveling range Certification according to 3-A Sanitary standards |
| Material | Stainless steel 1.4301 (AISI 304) |
| Supply includes | Assembly components and seals |
| Load capacity | Max. 7000 N static per leveling foot |
| Dimensions | Thread: M12 |
| Suitable for | Enclosure type: Compact enclosure HD VX VX SE TS |
| Leveling range | 122 - 175 mm 4.8 - 6.89 " |
| Packaging unit | 4 pc(s). |
| Net weight | 2.4 |
| Gross weight | 2.5 |
| Customs tariff number | 73181900 |
| EAN | 4028177707658 |
| ETIM 9 | EC002622 |

Features

| | |
|------------|----------|
| ETIM 8 | EC002622 |
| ECLASS 8.0 | 27189263 |