Rittal – The System.

Faster – better – everywhere.





HD 4000.285 Large enclosure

State: 11/6/2025 (Source: rittal.com/us-en)



HD 4000.285 - Large enclosure HD

The HD large enclosure is a bayable enclosure solution for hygienically sensitive areas that are subjected to regular cleaning.



Features

Model No.	HD 4000.285
Material	Housing and door: Stainless steel 1.4301 (AISI 304)
	HD lock inserts: Stainless steel 1.4404 (AISI 316L)
	Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600
	Mounting plate: Carbon steel
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height
	< 0.8 μm
	Mounting panel: Zinc-plated
	Seal: Blue, dyed (RAL 5010)
Supply includes	Enclosure frame with welded-on rear panel base plate
	Door with fitted seal
	Right-hand door catch on single-door enclosures may be swapped
	to the left
	Mounting panel
	Screwed-in middle bar
Options	HD supporting structure with leveling
Dimensions	Width: 1,200 mm
	Height: 1,800 mm
	Depth: 500 mm
	Width: 47.2 "
	Height: 70.9 "
	Depth: 19.7 "

© Rittal 2025

Features

Dimensions of mounting plate (W x H)	1,099 mm x 1,696 mm 43.3 ″ x 66.8 ″
Door opening angle	125°
IK code	IK08
Base material	Stainless steel 1.4301 (AISI 304)
Protection category IP to IEC 60 529	IP 66 IP X9
Protection category NEMA	NEMA 4X
Type rating according to UL 50E	Type 1 Type 3R Type 4X Type 12
Packaging unit	1 pc(s).
Net weight	148
Gross weight	149
Customs tariff number	94032080
EAN	4028177967960
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

	Approvals	UL + C-UL (listed)
--	-----------	--------------------

© Rittal 2025 3