
Rittal – The System.

Faster – better – everywhere.



SZ 4000.300

Pressure relief stoppers

State: 11/12/2026 (Source: www.rittal.com/us-en)

SZ 4000.300 - Pressure relief stoppers

Pressure relief plug in stainless steel, with integrated sealing membrane, specifically for exposure to changing climatic conditions (e.g. with outdoor installation).

Features

Model No.	SZ 4000.300
Product description	Pressure differences can cause condensation to form in sealed housings, especially when the housing is exposed to changing climatic conditions. The integrated sealing membrane in pressure relief plugs largely prevents these pressure differences and the build-up of condensate, as well as protecting against the penetration of moisture from outside. Installation is in vertical surfaces, to protect against dirt.
Technical specifications	Connection thread M12 x 1.5 Air permeability up to 60 liters/hour with a pressure difference of 70 mbar
Material	Stainless steel 1.4305 (AISI 303)
Supply includes	Incl. lock nut
Type rating according to 508A	Type 1 Type 4 Type 4X
Protection category IP to IEC 60 529	IP 66 IP X8 IP X9
Length	10 mm 0.39 ″
Packaging unit	5 pc(s).
Net weight	0.1 kg
Gross weight	0.12 kg
Customs tariff number	73269098
ETIM 9	EC002009

Features

ETIM 8	EC002009
ECLASS 8.0	27180715
Product description	SZ pressure relief stoppers, stainless steel, 1.4305

Approvals

Approvals	UR + C-UR (recognized)

© Rittal 2026