
# Rittal – The System.

Faster - better - everywhere.





# AS 4050.730 Wire end ferrule

State: 12/15/2025 (Source: rittal.com/us-en)



## AS 4050.730 - Wire end ferrule Loose

With plastic collar.

#### **Features**

Model No.	AS 4050.730
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	White
Length	8 mm 0.31 ″
AWG	20
Internal diameter	2.6 mm 0.1 ″
For cross section	0.5 mm²
DIN color code	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines.  For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Suitable for Model No.	4051.205 4051.210 4050.452
Delivery form	Loose
Packaging unit	500 pc(s).
Net weight	0.5
Gross weight	0.5
Customs tariff number	85369010

© Rittal 2025

### Features

EAN	4028177804982
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

# **Approvals**

Approvals	UL + C-UL (listed)
	UR

© Rittal 2025 3