


# Rittal – The System.

Faster – better – everywhere.



## AS 4050.735 Wire end ferrule

State: 12/10/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.735 - Wire end ferrule Loose

With plastic collar.

## Features

Model No.	AS 4050.735
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Gray
Length	10 mm 0.39 ~
AWG	12
Internal diameter	4.8 mm 0.19 ~
For cross section	4 mm <sup>2</sup>
DIN color code	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Suitable for Model No.	4051.210
Delivery form	Loose
Packaging unit	500 pc(s).
Net weight	0.5
Gross weight	0.5
Customs tariff number	85369010
EAN	4028177805033

# Features

ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

# Approvals

Approvals	UL + C-UL (listed) UR
-----------	--------------------------