

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.740 Wire end ferrule

State: 8/1/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.740 - Wire end ferrule Loose

With plastic collar.



## Features

Model No.	AS 4050.740
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Black
Length	12 mm 0.47 "
AWG	16
Internal diameter	3.5 mm 0.14 "
For cross section	1.5 mm <sup>2</sup>
DIN color code	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Suitable for Model No.	4051.205 4051.210
Delivery form	Loose (10 packs of 100)

# Features

Packaging unit	1,000 pc(s).
Net weight	1
Customs tariff number	85369010
EAN	4028177805088
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

# Approvals

Approvals	UL + C-UL (listed) UR
-----------	--------------------------