
## Rittal - The System.

Faster - better - everywhere.





# AS 4050.743 Wire end ferrule

State: 11/14/2025 (Source: rittal.com/us-en)



## AS 4050.743 - Wire end ferrule Loose

With plastic collar.

#### **Features**

Model No.	AS 4050.743
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Gray
Length	8 mm 0.31 ″
AWG	18
Internal diameter	3.4 mm 0.13 ″
For cross section	0.75 mm²
DIN color code	Yes
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Delivery form	Loose
Packaging unit	500 pc(s).
Net weight	0.5
Gross weight	0.049
Customs tariff number	85369010
EAN	4028177805118
ETIM 9	EC000005

© Rittal 2025

### Features

ETIM 8	EC000005
ECLASS 8.0	36659290

## **Approvals**

Approvals	UL + C-UL (listed)
	UR

© Rittal 2025 3