

Rittal – The System.

Faster – better – everywhere.



AS 4050.748

Wire end ferrule

State: 2/21/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.748 - Wire end ferrule on belt

With plastic flange.

Features

| | |
|--------------------------|--|
| Model No. | AS 4050.748 |
| Product description | With plastic flange. |
| Technical specifications | Heat resistant up to 105 °C |
| Material | E-Cu, tin-plated Plastic collar: Polypropylene |
| Color | Red |
| Length | 8 mm 0.31 " |
| AWG | 18 |
| Internal diameter | 3 mm 0.12 " |
| For cross section | 1 mm ² |
| DIN color code | Yes |
| Note | UL-certified in conjunction with the relevant tools, e.g. crimping machines. |
| Standards | AEH DIN 46228 |
| Delivery form | Taped |
| Packaging unit | 5,000 pc(s). |
| Net weight | 5 kg |
| Gross weight | 0.7 kg |
| Customs tariff number | 85369010 |
| ETIM 9 | EC000005 |
| ETIM 8 | EC000005 |
| ECLASS 8.0 | 36659290 |

Features

Product description

Wire end ferrules According to DIN colour code

Approvals

Approvals

UL + C-UL (listed)

UR