
# Rittal – The System.

Faster - better - everywhere.





# AS 4050.752 Wire end ferrule

State: 11/8/2025 (Source: rittal.com/us-en)



## AS 4050.752 - Wire end ferrule Loose

With plastic collar.

#### **Features**

Model No.	AS 4050.752
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated
	Plastic collar: Polypropylene
Color	Gray
Length	8 mm
	0.31 ~
AWG	26
Internal diameter	1.5 mm
	0.06 ″
Rittal color code	Yes
For cross section	0.14 mm²
Note	UL-certified in conjunction with the relevant tools, e.g. crimping
	machines.
	For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Delivery form	Loose
Packaging unit	500 pc(s).
Net weight	0.5
Customs tariff number	85369010
EAN	4028177815810
ETIM 9	EC000005
ETIM 8	EC000005

© Rittal 2025

### Features

ECLASS 8.0 36659290

# **Approvals**

Approvals UL + C-UL (listed) UR

© Rittal 2025

3