


# Rittal – The System.

Faster – better – everywhere.



## AS 4050.752 Wire end ferrule

State: 4/26/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.752 - Wire end ferrule Loose

With plastic collar.

## Features

Model No.	AS 4050.752
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Gray
Length	8 mm 0.31 "
AWG	26
Internal diameter	1.5 mm 0.06 "
Rittal color code	Yes
For cross section	0.14 mm <sup>2</sup>
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Delivery form	Loose
Packaging unit	500 pc(s).
Net weight	0.5 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

# Features

---

Product description

Wire end ferrules for manual preassembly, 0.14 mm<sup>2</sup>, AWG 26, 8 mm, grey, loosely packed, 500 pc(s).

# Approvals

---

Approvals

UL + C-UL (listed)  
UR