

Rittal – The System.

Faster – better – everywhere.



AS 4050.754 Wire end ferrule

State: 6/15/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.754 - Wire end ferrule Loose

With plastic collar.

Features

Model No.	AS 4050.754
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Light blue
Length	8 mm 0.31 "
AWG	24
Internal diameter	1.8 mm 0.07 "
Rittal color code	Yes
For cross section	0.25 mm ²
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Delivery form	Loose
Packaging unit	500 pc(s).
Net weight	0.5 kg
Gross weight	0.026 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005

Features

ECLASS 8.0

36659290

Product description

Wire end ferrules for manual preassembly, 0.25 mm², AWG 24, 8 mm, light blue, loosely packed, 500 pc(s).

Approvals

Approvals

UL + C-UL (listed)
UR