


# Rittal – The System.

Faster – better – everywhere.



## AS 4050.757 Wire end ferrule

State: 5/27/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.757 - Wire end ferrule Loose

With plastic collar.

## Features

Model No.	AS 4050.757
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Turquoise
Length	8 mm 0.31 "
AWG	22
Internal diameter	2 mm 0.08 "
Rittal color code	Yes
For cross section	0.34 mm <sup>2</sup>
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Delivery form	Loose
Packaging unit	500 pc(s).
Net weight	0.5 kg
Gross weight	0.026 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005

# Features

---

ECLASS 8.0	36659290
Product description	Wire end ferrules for manual assembly, 0.34 mm <sup>2</sup> , AWG 22, 8 mm, turquoise, loose, 500 pieces

---

# Approvals

---

Approvals	UL + C-UL (listed) UR
-----------	--------------------------