

Rittal – The System.

Faster – better – everywhere.



AS 4050.761

Wire end ferrule

State: 2/13/2026 (Source: rittal.com/us-en)

AS 4050.761 - Wire end ferrule Loose

With plastic collar.

Features

Model No.	AS 4050.761
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Orange
Length	10 mm 0.39 "
AWG	20
Internal diameter	2.6 mm 0.1 "
Rittal color code	Yes
For cross section	0.5 mm ²
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Suitable for Model No.	4051.205 4051.210
Delivery form	Loose
Packaging unit	500 pc(s).
Net weight	0.5
Gross weight	0.042
Customs tariff number	85369010

Features

EAN	4028177815773
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

Approvals

Approvals	UL + C-UL (listed) UR
-----------	--------------------------