

Rittal – The System.

Faster – better – everywhere.



AS 4050.767

Wire end ferrule

State: 1/10/2026 (Source: ittal.com/us-en)

AS 4050.767 - Wire end ferrule Loose

With plastic collar.

Features

Model No.	AS 4050.767
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	White
Length	12 mm 0.47 "
AWG	18
Internal diameter	2.8 mm 0.11 "
Rittal color code	Yes
DIN color code	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Delivery form	Loose
Packaging unit	500 pc(s).
Net weight	0.5
Customs tariff number	85369010
EAN	4028177999640
ETIM 9	EC000005
ETIM 8	EC000005

Features

ECLASS 8.0 36659290

Approvals

Approvals UL + C-UL (listed)
UR