

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.773 Wire end ferrule

State: 4/26/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.773 - Wire end ferrule Loose

With plastic collar.

## Features

|                          |  |
|--------------------------|--|
| Model No.                | AS 4050.773  |
| Product description      | With plastic collar.   |
| Technical specifications | Heat resistant up to 105 °C  |
| Material                 | E-Cu, tin-plated<br>Plastic collar: Polypropylene  |
| Color                    | Red  |
| Length                   | 8 mm<br>0.31 "   |
| AWG                      | 16   |
| Internal diameter        | 3.5 mm<br>0.14 "   |
| Rittal color code        | Yes  |
| For cross section        | 1.5 mm <sup>2</sup>  |
| Note                     | UL-certified in conjunction with the relevant tools, e.g. crimping machines.<br>For tailored advice, please contact a Rittal representative. |
| Standards                | AEH DIN 46228  |
| Suitable for Model No.   | 4051.205<br>4051.210<br>4050.452   |
| Delivery form            | Loose  |
| Packaging unit           | 500 pc(s).   |
| Net weight               | 0.5 kg   |
| Gross weight             | 0.058 kg   |
| Customs tariff number    | 85369010   |

# Features

---

|                     |   |
|---------------------|---|
| ETIM 9              | EC000005  |
| ETIM 8              | EC000005  |
| ECLASS 8.0          | 36659290  |
| Product description | Wire end ferrules for wire assembly, 1.5 mm <sup>2</sup> , AWG 16, 8 mm, red, loose, 500 pieces |

# Approvals

---

|           |                          |
|-----------|--------------------------|
| Approvals | UL + C-UL (listed)<br>UR |
|-----------|--------------------------|