
## Rittal – The System.

Faster - better - everywhere.





# AS 4050.773 Wire end ferrule

State: 12/10/2025 (Source: rittal.com/us-en)



## AS 4050.773 - Wire end ferrule Loose

With plastic collar.

#### **Features**

Model No.	AS 4050.773
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Red
Length	8 mm 0.31 ″
AWG	16
Internal diameter	3.5 mm 0.14 ″
Rittal color code	Yes
For cross section	1.5 mm²
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Suitable for Model No.	4051.205 4051.210 4050.452
Delivery form	Loose
Packaging unit	500 pc(s).
Net weight	0.5
Gross weight	0.058
Customs tariff number	85369010

© Rittal 2025 2

### Features

EAN	4028177815728
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

## **Approvals**

Approvals	UL + C-UL (listed)
	UR

© Rittal 2025 3