# Rittal - The System.

Faster - better - everywhere.





# AS 4050.776 Wire end ferrule

State: 11/24/2025 (Source: rittal.com/us-en)



## AS 4050.776 - Wire end ferrule Loose

With plastic collar.

#### **Features**

Model No.	AS 4050.776
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Red
Length	18 mm 0.71 ˝
AWG	16
Internal diameter	3.5 mm 0.14 ″
Rittal color code	Yes
DIN color code	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Delivery form	Loose
Packaging unit	500 pc(s).
Net weight	0.5
Customs tariff number	85369010
EAN	4028177999862
ETIM 9	EC000005
ETIM 8	EC000005

© Rittal 2025

### Features

ECLASS 8.0 36659290

## **Approvals**

Approvals UL + C-UL (listed) UR

© Rittal 2025

3